

TECHSPEC® 15mm Dia. x 25mm FL, NIR II Coated, Achromatic Lens



Stock **#45-826** 3-5 DAYS

- 1 + **A\$187.20**

ADD TO CART

Qty 1-5

A\$187.20

Qty 6+

A\$149.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):
25.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 19.49
Focal Length Specification Wavelength (nm) : 880.00
Clear Aperture CA (mm) : 14.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 9.35 ±0.20
Center Thickness CT 1 (mm) : 5.65 ±0.10
Center Thickness CT 2 (mm) : 3.70 ±0.10
Radius R₁ (mm) : 14.94
Radius R₂ (mm) : -14.94
Radius R₃ (mm) : -120.18
Edge Thickness ET (mm) : 7.10
Substrate : ☐ N-LAK22 / N-SF6
Surface Quality : 40-20
f/# : 1.67
Numerical Aperture NA : 0.30
Coating : NIR II (750-1550nm)
Coating Specification : R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 750 - 1550

Regulatory Compliance

RoHS 2015 : Compliant
Reach 224 : Compliant
Certificate of Conformance : View