

TECHSPEC[®] 18mm Dia. x 36mm FL, NIR I Coated, Double-Convex Lens



Stock **#49-486** 3-5 DAYS

[Other Coating Options](#)



1



A\$69.60

ADD TO CART

Qty 1-9

A\$69.60

Qty 10+

A\$62.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Back Focal Length BFL (mm):
34.59

Effective Focal Length EFL (mm): 36.00
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.80
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.55
Radius R₁=R₂ (mm): 36.60
Clear Aperture CA (mm): 17.00
f/#: 2.00
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.25
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View