

TECHSPEC® 20mm, 532nm V-Coat, Fused Silica High Power Laser Line RA Prism



Stock **#83-327** 3-5 DAYS

- 1 + **A\$259.20**

ADD TO CART

Qty 1-5
A\$259.20
Qty 6+
A\$207.20
Volume Pricing
Request Quote

Get Product Downloads



Angle Tolerance (arcsec):
±40

Coating:
Laser V-Coat (532nm)

Design Wavelength DWL (nm):
532

Substrate: ☐

Fused Silica (Corning 7980)
Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 28.30
Length of Legs (mm): 20.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Coating Specification: R _{abs} <0.25% @ 532nm
Ray Deviation (°): 90
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 20ns, 20Hz
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.20

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View