


TECHSPEC® 20mm Dia. x 30mm FL VIS 0° Coated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#49-977** 3-5 DAYS

- 1 +

A\$248.00

ADD TO CART

Qty 1-5

A\$248.00

Qty 6+

A\$198.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Back Focal Length BFL (mm): 25.88
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 6.00 ±0.10
Edge Thickness ET (mm): 1.69
Radius R₁ (mm): 13.75
Clear Aperture CA (mm): 19
f/#: 1.5
Numerical Aperture NA: 0.33
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant