

TECHSPEC® 20mm Dia. x 80mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-958-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 + **A\$182.40**

ADD TO CART

Qty 1-5
A\$182.40
Qty 6+
A\$146.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
20.00 ±0.025

Effective Focal Length EFL (mm):
80.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 77.26
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 19.00
Centering (arcmin): <1
Center Thickness CT (mm): 6.00 ±0.20
Center Thickness CT 1 (mm): 4.00 ±0.10
Center Thickness CT 2 (mm): 2.00 ±0.10
Radius R₁ (mm): 50.49
Radius R₂ (mm): -37.06
Radius R₃ (mm): -102.19
Edge Thickness ET (mm): 4.51
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 4.00
Numerical Aperture NA: 0.13
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View