

**TECHSPEC® 25.0mm Diameter x 150.0mm FL, 1064nm V-Coat, PCX Lens**



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#69-622** 3-5 DAYS

[Other Coating Options](#)

- 1 +

**A\$84.80**

ADD TO CART

Qty 1-9

A\$84.80

Qty 10+

A\$76.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



**Diameter (mm):**  
25.00 +0.0/-0.025

**Effective Focal Length EFL (mm):**

|                                                                                        |
|----------------------------------------------------------------------------------------|
| 150.00 @587.6nm                                                                        |
| <b>Back Focal Length BFL (mm):</b><br>147.81                                           |
| <b>Coating:</b><br>Laser V-Coat (1064nm)                                               |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.25% @ 1064nm                      |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a>                    |
| <b>Surface Quality:</b><br>40-20                                                       |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                  |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                            |
| <b>Focal Length Tolerance (%):</b><br>±1                                               |
| <b>Centering (arcmin):</b><br><1                                                       |
| <b>Center Thickness CT (mm):</b><br>3.50 ±0.10                                         |
| <b>Edge Thickness ET (mm):</b><br>2.49                                                 |
| <b>Radius R<sub>1</sub> (mm):</b><br>77.55                                             |
| <b>Clear Aperture CA (mm):</b><br>24                                                   |
| <b>f/#:</b><br>6.00                                                                    |
| <b>Numerical Aperture NA:</b><br>0.08                                                  |
| <b>Design Wavelength DWL (nm):</b><br>1064                                             |
| <b>Type:</b><br>Plano-Convex Lens                                                      |
| <b>Bevel:</b><br>Protective bevel as needed                                            |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>5 J/cm² @ 1064nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |