

25.4mm Dia. x 100mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) DCX Lens | CF-BX-25-100

See More by [ISP Optics](#)



Calcium Fluoride Double-Convex (DCX) Lenses

Stock #47-059 3-5 DAYS

- 1 + **A\$420.80**

ADD TO CART

Qty 1+
A\$420.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.13

Effective Focal Length EFL (mm):
100.00

Coating:
Uncoated

Substrate: Calcium Fluoride (CaF₂)
Surface Quality: 60-40
Clear Aperture (%) : 90.00
Centering (arcmin) : <3
Bevel: Protective bevel as needed
Center Thickness CT (mm) : 4.10
Center Thickness Tolerance (mm) : ±0.2
Edge Thickness ET (mm) : 2.00
Radius R₁=R₂ (mm) : 79.07
Back Focal Length BFL (mm) @DWL : 98.36
Effective Focal Length EFL @ 0.6328μm (mm) : 92.05
Effective Focal Length EFL @ 1.064μm (mm) : 92.99
Effective Focal Length EFL @ 2.94μm (mm) : 95.25
Effective Focal Length EFL @ 5.0μm (mm) : 100.00
f# : 3.94
Focal Length Specification Wavelength (μm) : 5.00
Focal Length Tolerance (%) : ±2 @DWL
Numerical Aperture NA : 0.13
Surface Accuracy : 1λ
Type : Double-Convex Lens
Wavelength Range (μm) : 0.35 - 7
Wavelength Range (nm) : 350 - 7000
Model Number : CF-BX-25-100

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View