

25.4mm Dia f/0.5 VIS Coated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#33-261** 3-5 DAYS

- 1 +

A\$112.00

ADD TO CART

Qty 1-10	A\$112.00
Qty 11+	A\$92.80
Volume Pricing	Request Quote

Get Product Downloads

Diameter (mm):
25.40 ±0.1

Effective Focal Length EFL (mm):
12.70 @ 632.8nm

Numerical Aperture NA:

1.00
Back Focal Length BFL (mm): 8.00
Substrate: ☐ PMMA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 632.8
Coating: BBAR (450-650nm)
Coating Specification: Ravg <0.5% @ 450 - 650nm
Clear Aperture CA (mm): 23.9
Edge Thickness ET (mm): 4.00
Center Thickness CT (mm): 13.67
f#: 0.5
Bevel: Protective bevel as needed
Operating Temperature (°C): 80.00
Radius R (mm): 74.68
Type: Aspheric Lens
Wavelength Range (nm): 450 - 650
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View