

TECHSPEC®

25.4mm Dia. x 63.5mm FL, NIR I Coated, Plano-Convex Lens



Stock #62-587 3-5 DAYS

[Other Coating Options](#)



1



A\$66.40

ADD TO CART

Qty 1-9

A\$66.40

Qty 10+

A\$59.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40 +0.0/-0.025

Effective Focal Length EFL (mm):
63.50 @ 587.6nm

Back Focal Length BFL (mm): 60.37
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.75 ±0.10
Edge Thickness ET (mm): 2.19
Radius R₁ (mm): 32.82
Clear Aperture CA (mm): 24.4
f/#: 2.5
Numerical Aperture NA: 0.20
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant