

TECHSPEC[®] 25mm, Protected Gold Coated, N-BK7 90° Specialty Mirror



Stock **#47-238** [CONTACT US](#)

-

1

+

A\$288.00

ADD TO CART

Qty 1-5

A\$288.00

Qty 6+

A\$230.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Clear Aperture CA (mm):
24.0

Coating:
Protected Gold (700-10000nm)

Substrate:

N-BK7

Surface Quality:

40-20
Type: Right Angle Mirror
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture (%) : 90.00
Length of Hypotenuse (mm): 35.40
Length of Legs (mm): 25.00
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Wavelength Range (nm): 700 - 10000
Coating Type: Metal
Damage Threshold, Reference: ☐ 0.8 J/cm ² @ 1064nm, 10ns
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
