

TECHSPEC® 25mm Dia 0.42 NA, Uncoated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#48-537** 3-5 DAYS

[Other Coating Options](#)

− 1 +

A\$824.00

ADD TO CART

Qty 1-5

A\$824.00

Qty 6+

A\$659.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):

30.00 @ 587.6nm
Numerical Aperture NA: 0.42
Back Focal Length BFL (mm): 24.17
Substrate: Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 2.21
Center Thickness CT (mm): 8.50 ±0.1
f/#: 1.2
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 200 - 2200
Conjugate Distance: Infinite
Power (diopters): 33.33

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View