


TECHSPEC[®] 30mm Dia. x 120mm FL UV-VIS Coated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#84-305** 3-5 DAYS

- 1 +

A\$296.00

ADD TO CART

Qty 1-5

A\$296.00

Qty 6+

A\$236.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.025

Effective Focal Length EFL (mm):
120.00 @587.6nm

Back Focal Length BFL (mm): 116.57
Coating: UV-VIS (250-700nm)
Coating Specification: R _{abs} ≤1.0% @ 350 - 450nm R _{avg} ≤1.5% @ 250 - 700nm
Substrate: Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 5.00 ±0.10
Edge Thickness ET (mm): 2.92
Radius R₁ (mm): 55.02
Clear Aperture CA (mm): 29
f/#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: View 3 J/cm ² @ 355nm, 10ns 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant