

TECHSPEC®

25mm Dia. x 150mm FL, VIS-NIR Coated, Double-Convex Lens



Stock **#45-894** 3-5 DAYS

[Other Coating Options](#)



1



A\$80.00

ADD TO CART

Qty 1-9

A\$80.00

Qty 10+

A\$72.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Back Focal Length BFL (mm):
148.88

Effective Focal Length EFL (mm): 150.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.40
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.39
Radius R₁=R₂ (mm): 154.52
Clear Aperture CA (mm): 24.00
f/#: 6.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.08
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant