

TECHSPEC® 35.0mm Dia., 1mm Thick, Uncoated, Sapphire Window



Stock #48-920

3-5 DAYS

-

1

+

A\$336.00

ADD TO CART

Qty 1-24

A\$336.00

Qty 25+

A\$268.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Abbe Number (v_d):
72.24

Axis Orientation:
Random

Bevel:
Protective as needed

Birefringence (n_o - n_e):

0.008 for Visible Light Orthogonal to Optical Axis
Clear Aperture (%) : ≥90
Clear Aperture CA (mm) : 31.50
Diameter (mm) : 35.00 ±0.25
Thickness (mm) : 1.00 ±0.10
Coating : Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 8.8
Density (g/cm³) : 3.97
Edges : Fine Ground
Index of Refraction n_d : 1.77
Knoop Hardness (kg/mm²) : 1900
Parallelism (arcmin) : ≤3.5
Poisson's Ratio : 0.27
Substrate : Sapphire (Al ₂ O ₃)
Surface Flatness (P-V) : 2λ (typical)
Surface Quality : 80-50
Type : Protective Window
Wavelength Range (nm) : 330 - 5500
Young's Modulus (GPa) : 435

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 240 : Compliant