

TECHSPEC® 25mm Dia x 50mm FL NIR I Coated, Illumination Grade PCX Cylinder Lens



Stock #69-753

3-5 DAYS

-

1

+

A\$140.80

ADD TO CART

Qty 1-5

A\$140.80

Qty 6+

A\$112.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
50.00

Substrate:

N-BK7

f/#:

Numerical Aperture NA: 0.25
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): 47.20
Center Thickness CT (mm): 4.24
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.03
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 25.93
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant