

TECHSPEC® 38.1 x 38.1mm Protected Gold, 4-6λ Mirror



Stock **#83-498** 3-5 DAYS

- 1 + **A\$113.60**

ADD TO CART

Qty 1-5
A\$113.60
Qty 6+
A\$90.40
Volume Pricing
Request Quote

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):
38.1 x 38.1

Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 36.20 x 36.20
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Length (mm): 38.10
Width (mm): 38.10
Damage Threshold, By Design: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant