

TECHSPEC® 40mm Dia., 0.80 Numerical Aperture Uncoated, Aspheric Lens



Stock **#67-247** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$864.00

ADD TO CART

Qty 1-5
A\$864.00
Qty 6+
A\$691.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.1

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Numerical Aperture NA:
0.80

Back Focal Length BFL (mm): 15.73
Substrate: N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 36
Edge Thickness ET (mm): 1.49
Center Thickness CT (mm): 15.50 ±0.1
f/#: 0.63
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 380 - 2500
Conjugate Distance: Infinite
Power (diopters): 40.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View