

2.95μm CWL, 25.0mm Diameter, 0.11 FWHM, IR Bandpass Filter



Stock #84-070 3-5 DAYS

-

1

+

A\$692.80

ADD TO CART

Qty 1-9

A\$692.80

Qty 10+

A\$624.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm):
21.0

Center Wavelength CWL (nm): 2,950.00 ±30
Full Width-Half Max FWHM (nm): 110.00
Substrate: ☐ Sapphire (Al ₂ O ₃)
Coating: Traditional Coated
Surface Quality: 60-40
Thickness (mm): 1.00 ±0.2
Transmission (%): 65 (minimum)
Type: Bandpass Filter
Typical Applications: Water Vapor Emission
Blocking Wavelength Range (nm): 200 - 30000
Center Wavelength CWL (μm): 2.95 ±0.03
Full Width-Half Max FWHM (μm): 0.11 ±0.03

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant