

TECHSPEC® 2" Dia, 12" FL Uncoated, Spherical Mirror



Stock #32-817 3-5 DAYS

⊖ 1 ⊕ **A\$192.00**

ADD TO CART

Qty 1-9

A\$192.00

Qty 10+

A\$163.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Substrate: BOROFLOAT®

Focal Length Tolerance (%): ±2

Surface Quality: 60-40

Surface Accuracy:

λ/4

Diameter (inches):

2.0

Diameter (mm):

50.80 +0.5/-0

Diameter Tolerance (inches):

+0.02/-0

Effective Focal Length EFL (inches):

12.00

Effective Focal Length EFL (mm):

304.80

Radius of Curvature (mm):

609.60

Aperture (f/#):

f/6

Coating:

Uncoated

Coating Type:

Uncoated

Back Surface:

Ground

Edge Thickness ET (inches):

0.50

Edge Thickness ET (mm):

12.70

Edge Thickness Tolerance (%):

+0.0/-15

Type:

Spherical Mirror

Regulatory Compliance

RoHS 2015:[Compliant](#)**Reach 219:**[Compliant](#)**Certificate of Conformance:**[View](#)