

TECHSPEC®

4.0mm Dia. x 8.0mm FL, VIS-NIR Coated, Plano-Convex Lens



Stock #47-852

3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$100.80

ADD TO CART

Qty 1-9

A\$100.80

Qty 10+

A\$90.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):

4.00 +0.0/-0.025

Effective Focal Length EFL (mm):

8.00 @ 587.6nm

Back Focal Length BFL (mm): 7.17
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BAF10
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.39 ±0.05
Edge Thickness ET (mm): 1.00
Radius R₁ (mm): 5.36
Clear Aperture CA (mm): 3.6
f#: 2.00
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant