

TECHSPEC® 4.25" Diameter x 34" FL Enhanced Aluminum, Parabolic Mirror



Stock **#32-067-533** 3-5 DAYS

- 1 +

A\$777.60

ADD TO CART

Qty 1-9

A\$777.60

Qty 10+

A\$660.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Substrate: ☐ **BOROFLOAT®**

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 4.25 +0.06/-0
Diameter (mm): 108.00 +1.5/-0
Effective Focal Length EFL (inches): 34.0
Effective Focal Length EFL (mm): 863.60
Radius of Curvature (mm): 1,727.20
Aperture (f/#): f/8
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R_{avg} >95% @ 450 - 650nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 98
Edge Thickness ET (inches): 0.75
Edge Thickness ET (mm): 19.10
Type: Parabolic Mirror
Wavelength Range (μm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant