

TECHSPEC® 458nm, 12.5 x 17.6mm, Dichroic Filter



TECHSPEC® Fluorescence Dichroic Filters

Stock **#67-062** 3-5 DAYS

- 1 + **A\$297.60**

ADD TO CART

Qty 1-5

A\$297.60

Qty 6+

A\$233.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
12.5 x 17.6

Angle of Incidence (°):
45

Cut-On Wavelength (nm):
458.00 ±4.0

Substrate: Fused Silica (Coming 7980)
Length (mm): 17.60
Coating: Hard Coated
Reflection (%): 98.00 (average)
Reflection Wavelength (nm): 415 - 450
Surface Quality: 60-40
Thickness (mm): 1.05
Thickness Tolerance (mm): ±0.1
Transmission (%): 90.00 (average)
Transmission Wavelength (nm): 467 - 600
Type: Dichroic Filter
Width (mm): 12.50
Dimensional Tolerance (mm): +0.0/-0.2
Transmitted Wavefront, RMS: 1λ
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Wavelength Range (nm): 415 - 600

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant