


TECHSPEC® 6" Dia. λ /20 Fused Silica Dual Surface Flat



Stock #48-133

3-5 DAYS

-

1

+

A\$5,312.00

ADD TO CART

Qty 1+
A\$5,312.00
Volume Pricing
Request Quote

Get Product Downloads

Surface Flatness (P-V):
 λ /20

Abbe Number (v_d):
67.8

Coating:
Uncoated

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
0.52 (+5 to +35°C)
0.57 (0 to +200°C)

0.48 (-100 to +200°C)
Diameter (mm): 152.40 ±1.0
Thickness (mm): 25.40 ±2.0
Diameter (inches): 6.00 ±0.04
Thickness (inches): 1.00 ±0.08
Clear Aperture CA (mm): 137.20
Construction: Dual Surface
Density (g/cm³): 2.20
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcmin): ≤1
Poisson's Ratio: 0.16
Substrate: Fused Silica (Corning 7980)
Surface Quality: 60-40
Type: Interferometry Window
Wavelength Range (nm): 200 - 2200
Young's Modulus (GPa): 73
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View