

TECHSPEC[®] 6.0mm Dia. x 24.0mm FL, NIR I, Inked, Plano-Convex Lens



Stock **#48-720-INK** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$75.20

ADD TO CART

Qty 1-9

A\$75.20

Qty 10+

A\$67.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.00 ±0.025

Effective Focal Length EFL (mm):
24.00 @ 587.6nm

Back Focal Length BFL (mm): 23.01
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.50 ±0.05
Edge Thickness ET (mm): 1.13
Radius R₁ (mm): 12.40
Clear Aperture CA (mm): 5.4
f/#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View