

TECHSPEC® 50mm Dia. x 300mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#49-288-INK** 3-5 DAYS

[Other Coating Options](#)



1



A\$304.00

ADD TO CART

Qty 1-5

A\$304.00

Qty 6+

A\$243.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 ±0.025

Effective Focal Length EFL (mm):
300.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 292.91
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 49.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 12.50 ±0.20
Center Thickness CT 1 (mm) : 9.00 ±0.10
Center Thickness CT 2 (mm) : 3.50 ±0.10
Radius R₁ (mm) : 173.11
Radius R₂ (mm) : -164.03
Radius R₃ (mm) : -709.83
Edge Thickness ET (mm) : 10.24
Substrate : ☐ N-BAK4 / N-SF10
Surface Quality : 40-20
f/# : 6.00
Numerical Aperture NA : 0.08
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View