

TECHSPEC[®] 6mm Dia. x -12mm FL, MgF₂ Coated, Double-Concave Lens



Stock #48-687 3-5 DAYS

[Other Coating Options](#)



1



A\$53.60

ADD TO CART

Qty 1-9

A\$53.60

Qty 10+

A\$48.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-12.00

Substrate: N-BK7
f#: 2.00
Numerical Aperture NA: 0.25
Coating: MgF ₂ (400-700nm)
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): -12.33
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 5.4
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Edge Thickness ET (mm): 1.59
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -12.57
Surface Quality: 40-20
Damage Threshold, By Design: 10 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant