

TECHSPEC® 76.2mm Dia Protected Gold, 4-6λ Mirror



Stock **#83-501** 3-5 DAYS

- 1 + **A\$177.60**

ADD TO CART

Qty 1-5
A\$177.60
Qty 6+
A\$135.20
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
76.20 ±0.25

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 72.39
Edges: Ground, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00 nominal
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Damage Threshold, By Design: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant