

TECHSPEC<sup>®</sup> 6.0mm Diameter x 9.0mm FL, 405nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#66-254** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$72.80

ADD TO CART

Qty 1-9

A\$72.80

Qty 10+

A\$65.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):  
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):

|                                                                                       |
|---------------------------------------------------------------------------------------|
| 9.00 @ 587.6nm                                                                        |
| <b>Back Focal Length BFL (mm):</b><br>7.95                                            |
| <b>Coating:</b><br>Laser V-Coat (405nm)                                               |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.25% @ 405nm                      |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-SF5</a>                   |
| <b>Surface Quality:</b><br>40-20                                                      |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                 |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                           |
| <b>Focal Length Tolerance (%):</b><br>±1                                              |
| <b>Centering (arcmin):</b><br><3                                                      |
| <b>Center Thickness CT (mm):</b><br>1.75 ±0.05                                        |
| <b>Edge Thickness ET (mm):</b><br>0.95                                                |
| <b>Radius R<sub>1</sub> (mm):</b><br>6.05                                             |
| <b>Clear Aperture CA (mm):</b><br>5.4                                                 |
| <b>f/#:</b><br>1.5                                                                    |
| <b>Numerical Aperture NA:</b><br>0.33                                                 |
| <b>Design Wavelength DWL (nm):</b><br>405                                             |
| <b>Type:</b><br>Plano-Convex Lens                                                     |
| <b>Bevel:</b><br>Protective bevel as needed                                           |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>3 J/cm² @ 405nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |