


TECHSPEC<sup>®</sup> 900nm, 25mm Diameter, Dichroic Shortpass Filter



TECHSPEC Dichroic Shortpass Filters

Stock #69-210 3-5 DAYS

-

1

+

A\$273.60

ADD TO CART

Qty 1-5

A\$273.60

Qty 6+

A\$214.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):  
25.00

Angle of Incidence (°):  
45

Cut-Off Wavelength (nm):  
900.00

|                                                                                                                                                                                                             |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div><div>Substrate:</div><div><div><div></div></div><div>Fused Silica</div></div><div>(Coming 7980)</div></div>                                                                                            |
| <div><div>Coating:</div><div>Hard Coated</div></div>                                                                                                                                                        |
| <div><div>P-Polarization Transmission (%)</div><div>&gt;80</div></div>                                                                                                                                      |
| <div><div>Reflection (%)</div><div>&gt;97 Average Polarization</div></div>                                                                                                                                  |
| <div><div>Reflection Wavelength (nm)</div><div>960 - 1170</div></div>                                                                                                                                       |
| <div><div>S-Polarization Transmission (%)</div><div>&gt;80</div></div>                                                                                                                                      |
| <div><div>Surface Quality:</div><div>60-40</div></div>                                                                                                                                                      |
| <div><div>Thickness (mm)</div><div>1.05</div></div>                                                                                                                                                         |
| <div><div>Thickness Tolerance (mm)</div><div>±0.1</div></div>                                                                                                                                               |
| <div><div>Transmission (%)</div><div>&gt;85 Average Polarization</div></div>                                                                                                                                |
| <div><div>Transmission Wavelength (nm)</div><div>465 - 865</div></div>                                                                                                                                      |
| <div><div>Type:</div><div>Dichroic Filter</div></div>                                                                                                                                                       |
| <div><div>Dimensional Tolerance (mm)</div><div>+0.0/-0.2</div></div>                                                                                                                                        |
| <div><div>Transmitted Wavefront, RMS:</div><div><math>\lambda/4</math></div></div>                                                                                                                          |
| <div><div>Slope Factor (%)</div><div>3.00</div></div>                                                                                                                                                       |
| <div><div>Cut-Off Tolerance (%)</div><div>±2</div></div>                                                                                                                                                    |
| <div><div>S-Polarization Reflection (%)</div><div>&gt;95</div></div>                                                                                                                                        |
| <div><div>P-Polarization Reflection (%)</div><div>&gt;95</div></div>                                                                                                                                        |
| <div><div>Environmental Durability:</div><div>Humidity per MIL-STD-810H, Section 507.6<br/>Temperature per MIL-STD-810H, Section 501.7 and 502.7</div></div>                                                |
| <div><div>Physical Durability:</div><div>Adhesion per MIL-PRF-13830B, Section C.4.5.12<br/>Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11<br/>Cleaning per MIL-C-48497A Section 4.5.4.2</div></div> |
| <div><div>Coating Specification:</div><div>Surface 1: Hard Dielectric Sputtered<br/>Surface 2: MgF<sub>2</sub></div></div>                                                                                  |
| <div><div>Wavelength Range (nm)</div><div>465 - 1170</div></div>                                                                                                                                            |

## Regulatory Compliance

|                                                                  |
|------------------------------------------------------------------|
| <div><div>RoHS 2015:</div><div>Compliant</div></div>             |
| <div><div>Certificate of Conformance:</div><div>View</div></div> |
| <div><div>Reach 240:</div><div>Compliant</div></div>             |