

TECHSPEC® 660nm, 25.0mm Diameter, Dichroic Filter



TECHSPEC® Fluorescence Dichroic Filters

Stock **#67-076** CLEARANCE 3-5 DAYS

- 1 +

A\$144.00

ADD TO CART

Qty 1+

A\$144.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):
45

Cut-On Wavelength (nm):
660.00

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:

Hard Coated
Reflection (%): 98.00 (average)
Reflection Wavelength (nm): 580 - 651
Surface Quality: 60-40
Thickness (mm): 1.05
Thickness Tolerance (mm): ±0.1
Transmission (%): 90.00 (average)
Transmission Wavelength (nm): 670 - 800
Type: Dichroic Filter
Dimensional Tolerance (mm): +0.0/-0.2
Transmitted Wavefront, RMS: 1λ
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Wavelength Range (nm): 580 - 800

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View