

TECHSPEC[®] 9mm Dia. x 13.5mm FL, NIR II Coated, Double-Convex Lens



Stock #67-609 3-5 DAYS

[Other Coating Options](#)



1



A\$64.80

ADD TO CART

Qty 1-9

A\$64.80

Qty 10+

A\$58.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Back Focal Length BFL (mm):
12.56

Effective Focal Length EFL (mm): 13.50
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Center Thickness CT (mm): 2.75
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.2
Radius R₁=R₂ (mm): 13.46
Clear Aperture CA (mm): 8.10
f/#: 1.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, Reference: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant