

TECHSPEC® Finite Conjugate, UV Coated, 15X/0.28NA HP ReflX



High Performance ReflX™ Objectives

Stock **#59-887** [CONTACT US](#)



1



A\$3,934.40

ADD TO CART

Qty 1+

A\$3,934.40

Qty 2+

A\$3,472.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Entrance Pupil Position (mm):

40.0

Field of View (mm):

150

Horizontal Field of View, 1/2" Sensor:

0.43mm

Horizontal Field of View, 2/3" Sensor:

0.59mm
Focal Length FL (mm): 12.97
Coating: Enhanced Aluminum (200-11000nm)
Magnification: 15X
Mount: RMS
Numerical Aperture NA: 0.28
Type: Microscope Objective
Obscuration (%): 27.00
Transmitted Wavefront, RMS: <i>N</i> /14
Diameter of Small Mirror (mm): 8.8
Working Distance (mm): 23.75
Aperture Diameter (mm): 8.5
Note: Entrance Pupil Position specification is measured in mm from flange
Coating Specification: R _{avg} >85% @ 200 - 700nm (typical) R _{avg} >76% @ 700 - 1750nm (typical) R _{avg} >96% @ 1750 - 11000nm (typical)
Wavelength Range (nm): 200 - 11000
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Flange Distance (mm): 150

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View