

TECHSPEC[®] 9.0mm Diameter x 13.5mm FL, 1550nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#84-220** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$74.40

ADD TO CART

Qty 1-9

A\$74.40

Qty 10+

A\$66.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):

13.50 @ 587.6nm
Back Focal Length BFL (mm): 11.94
Coating: Laser V-Coat (1550nm)
Coating Specification: R _{abs} <0.25% @ 1550nm
Substrate: ☐ N-SF5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.60 ±0.05
Edge Thickness ET (mm): 1.41
Radius R₁ (mm): 9.09
Clear Aperture CA (mm): 8.1
f/#: 1.5
Numerical Aperture NA: 0.33
Design Wavelength DWL (nm): 1550
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 5 J/cm² @ 1550nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant