

LightPath 390037 | 5.5mm Dia., 0.85 NA, BBAR (1800-3000nm), Mounted IR Aspheric Lens

See More by [Lightpath®](#)



Stock #66-572 CLEARANCE 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$375.92

ADD TO CART

Qty 1+

A\$375.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
5.50 ±0.10

Effective Focal Length EFL (mm):
1.87 @ 9500nm

Numerical Aperture NA:
0.85

Substrate: ☐
Black Diamond™ BD-2 (Ge₂₈Sb₁₂Se₆₀)

Aspheric Design Wavelength (nm):

9500
Coating: BBAR (1800-3000nm)
Coating Specification: R _{avg} <1.0% @ 1.8 - 3.0µm
Surface Quality: 80-50
Clear Aperture CA (mm): 4.00
Center Thickness CT (mm): 3.00
f/#: 0.58
Bevel: Protective bevel as needed
Density (g/cm³): 4.68
Index of Refraction n_d @ 10µm: 2.6023
Index of Refraction n_d @ 14µm: 2.5843
Index of Refraction n_d @ 4µm: 2.6210
Index of Refraction n_d @ 5µm: 2.6173
Lightpath Lens Code: 390037
Mount: Stainless Steel, M9 x0.5 Thread
Thermo-optic coefficient dn/dT: 70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 µm)
Transformation Temperature (°C): 285.00
Type: Aspheric Lens
Wavelength Range (nm): 1800 - 3000
Working Distance (mm): 0.72
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant