


TECHSPEC® Achromatic Lenses


TECHSPEC® ACHROMATIC LENSES

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy



+ 0.4861
x 0.5876
□ 0.6563




SPOT DIAGRAM	
SUBSURFACE: INA	DATA: 0.000 NM
TUE DEC 16 2008 UNITS ARE μm.	
FIELD	
RMS RADIUS : 30.280	
GEO RADIUS : 87.031	
SCALE BAR : 200	REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)

CHROMATIC FOCAL SHIFT

49285
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 350.5159 μm
DIFFRACTION LIMITED RANGE: 21.171 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)



EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)

POLYCHROMATIC DIFFRACTION MTF

49285
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm.
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)