


TECHSPEC® Achromatic Lenses


Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



+ 0.4861
x 0.5876
■ 0.6563



SURFACE: INA

IPA: 0.000 MM

SPOT DIAGRAM

49778INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 165.055
GD RADIUS : 385.078
SCALE BAR : 1000


REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

CHROMATIC FOCAL SHIFT

49778INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 157.4346 μm
DIFFRACTION LIMITED RANGE: 5.462 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)




TRANSVERSE RAY FAN PLOT

49778INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 1000.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



POLYCHROMATIC DIFFRACTION MTF

49778INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

EO Edmund
optics | worldwide

www.edmundoptics.com