




NOTES:

1. SUBSTRATE MATERIAL:  
BOROFLOAT®
2. CLEAR APERTURE AND COATING APERTURE  
ARE CENTERED ON SURFACES
3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: T(avg) >90% @ 400 - 690nm  
R(avg) >95% @ 750 - 1150nm

S2: R(avg) <1% @ 400 - 700nm



4. FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	S1	S2	 <b>Edmund Optics®</b>			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	80-50	80-50	THIRD ANGLE PROJECTION 	TITLE	25.0 x 25.0mm, 0° AOI, HOT MIRROR	
SURFACE FLATNESS	4 - 6λ	4 - 6λ		DWG NO	64458	SHEET 1 OF 1
CLEAR APERTURE	24 x 24	24 x 24				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm		