


# TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SURFACE: INR


IMA: 0.030 NM

SPOT DIAGRAM

49772  
TUE DEC 16 2008 UNITS ARE μm.  
FIELD : 82.157  
RMS RADIUS : 191.760  
SCALE BAR : 400

REFERENCE : CHIEF RAY


EDMUND OPTICS  
[HTTP://WWW.EDMONDOPTICS.COM](http://www.edmundoptics.com)



CHROMATIC FOCAL SHIFT

49772  
TUE DEC 16 2008  
MAXIMUM FOCAL SHIFT RANGE: 78.8256 μm  
DIFFRACTION LIMITED RANGE: 5.464 μm  
PUPIL ZONE: 0.0000

EDMUND OPTICS  
[HTTP://WWW.EDMONDOPTICS.COM](http://www.edmundoptics.com)




TRANSVERSE RAY FAN PLOT

49772  
TUE DEC 16 2008  
MAXIMUM SCALE: ± 500.000 μm.  
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS  
[HTTP://WWW.EDMONDOPTICS.COM](http://www.edmundoptics.com)



POLYCHROMATIC DIFFRACTION MTF

49772  
TUE DEC 16 2008  
DATA FOR 0.4250 TO 0.6750 μm.  
SURFACE: IMAGE

EDMUND OPTICS  
[HTTP://WWW.EDMONDOPTICS.COM](http://www.edmundoptics.com)