

TECHSPEC® GOLD SERIES FOCUSABLE TELECENTRIC LENS

#55-348 • 132 - 182mm WD • 0.125X

TECHSPEC® GOLD SERIES FOCUSABLE TELECENTRIC LENS

Important tools for machine vision systems and metrology applications, TECHSPEC® Gold Series Focusable Telecentric Lenses yield images from which precise measurements can be taken. These lenses yield constant magnification over a defined depth of field and are optimized to provide $<0.2^\circ$ telecentricity when used in the specified working distance range. Anywhere within the specified working distance, the same magnification can be obtained simply by refocusing. Both the aperture and focusing adjustment positions can be fixed by set screws to remain secure in high vibration environments.



Primary Magnification:	0.125X
Working Distance¹:	132 - 182mm
Depth of Field²:	$\pm 30.4\text{mm}$ at f10 (20% @ 20 lp/mm)
Length:	200.0mm
Filter Thread:	M105 x 1.0
Max. Sensor Format:	$\frac{2}{3}"$
Camera Mount:	C-Mount

Telecentricity:	$<0.1^\circ$
Distortion:	$<0.5\%$
Resolution²:	$>45\%$ @ 40 lp/mm
Aperture (f/#):	f/6 - f/17.4, lockable
Object Space NA:	0.010
Number of Elements (Groups):	10 (8)
AR Coating:	425 - 675nm BBAR
Weight:	2.66kg

Sensor Size	$\frac{1}{4}"$	$\frac{1}{3}"$	$\frac{1}{2.5}"$	$\frac{1}{2}"$	$\frac{1}{1.8}"$	$\frac{2}{3}"$	1"	$\frac{4}{3}"$
Field of View³	27.6mm	36.8mm	43.7mm	49.0mm	55.0mm	67.4mm	N/A	N/A

1. From front of housing 2. Image space MTF contrast 3. Horizontal FOV on standard 4:3 sensor format

Specifications subject to change




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® GOLD SERIES FOCUSABLE TELECENTRIC LENS

#55-348 • 132 - 182mm WD • 0.125X

MTF & DOF: f/6.0




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). The depth of field at the maximum sensor format for the plotted frequency and $f/\#$ at 20% contrast is indicated by the measurement bars.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® GOLD SERIES FOCUSABLE TELECENTRIC LENS

#55-348 • 132 - 182mm WD • 0.125X

MTF & DOF: f/10.0




Figure 5: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 6: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). The depth of field at the maximum sensor format for the plotted frequency and $f/\#$ at 20% contrast is indicated by the measurement bars.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.