

NOTES:



1. SUBSTRATE MATERIAL: GRADE A FINE ANNEALED
SCHOTT: BOROFLOAT® 472/657

2. COATING (APPLY ACROSS CLEAR APERTURE)
SPECIFICATIONS APPLY FOR 0° AOI

S1: T(AVG) > 90% FROM 400-690nm
R(AVG) > 95% FROM 710-1150nm

S2: R(AVG) < 1.0% FROM 400-700nm

3. EDGES: CUT, SHARP EDGES REMOVED



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

			EFL (AT 587.6nm)	NA	Edmund Optics®		
SHAPE	S1 PLANO	S2 PLANO	BFL (AT 587.6nm)	NA	TITLE	0° AOI, 20mm Square, Hot Mirror	
SURFACE ACCURACY AT 632.8nm (P-V)	4-6 WAVES PER INCH	4-6 WAVES PER INCH	ALL DIMS IN	mm	DWG NO	64456	SHEET 1 OF 1
SURFACE QUALITY	80 - 50	80 - 50					
MIN CLEAR APERTURE	19.00 x 19.00	19.00 x 19.00					