

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

NOTES:

1. SUBSTRATE  
UV GRADE FUSED SILICA
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 ARCSEC
3. COATING (APPLY ACROSS COATING APERTURE)


PERFORMANCE SPECIFICATIONS @ 0° AOI  
T(AVG): >85% FROM 1290 - 2000nm  
T(AVG): < 1% FROM 960 - 1200nm  
T(ABS): = 50% @ 1250nm

S1: MULTILAYER DIELECTRIC COATING  
S2: SINGLE LAYER MgF2


4. FINE GRIND SURFACE

5. TRANSMITTED WAVEFRONT DISTORTION RMS@ 632.8nm ≤ ¼ WAVE

6. ROHS COMPLIANT



LONGPASS FILTER




SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	80%	80%
COATING APERTURE	Ø20.00	Ø20.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

**Edmund Optics®**

THIRD ANGLE  
PROJECTION



TITLE

OD2, Ø25mm, 1250nm LONGPASS FILTER

DWG NO

84673

SHEET  
1 OF 1