




NOTES:

- 1. SUBSTRATE : GERMANIUM (GE)
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
 S1: UNCOATED
 S2: UNCOATED

3. FINE GRIND SURFACE




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
CLEAR APERTURE	85%	85%
ANGLE TOL. (arcmin)	±10	±10
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	2λ	2λ
WAVELENGTH RANGE (nm)	2000 - 14000	2000 - 14000
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION



ALL DIMS IN

mm



TITLE

GERMANIUM, 25.4mm, UNCOATED, IR RIGHT ANGLE PRISM

DWG NO

64120

SHEET
1 OF 1