





NOTES:

- 1. COATING (APPLY ACROSS CLEAR APERTURE)  
LASER V-COAT  
R(abs) 0.25% @ 355 nm
- 2. RoHS COMPLIANT



Ø 58.2

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	
DAMAGE THRESHOLD (PULSED)	1 J/cm <sup>2</sup> @ 10ns, 20Hz, 355nm
DESIGN WAVELENGTH DWL (nm)	355
TRANSMISSION	>95% @ DWL
TRANSMITTED WAVEFRONT, P-V	<λ/4 @ 355nm for Input Beam ≤5mm



ALL DIMS IN

mm

**Edmund Optics®**

TITLE

355 nm 1X - 3X VARIABLE BEAM EXPANDER

DWG NO

87560

SHEET  
1 OF 1