



1. SUBSTRATE MATERIAL:
N-BK7

- S1 & S2: VIS-NIR (400-1000nm)
 $R(ABS) \leq 0.25\% @ 880nm$
 $R(AVG) \leq 1.25\% @ 400 - 870nm$
 $R(AVG) \leq 1.25\% @ 890 - 1000nm$



3. FINE GROUND SURFACE

- #### 4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	150			
SHAPE	CONVEX	PLANO	BFL	148.02			
RADIUS	77.52	INFINITY			TITLE	25.4mm H X 25.4mm L X 150mm FL VIS-NIR, CYLINDER LENS	
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	22.86 x 22.86	22.86 x 22.86	ALL DIMS IN mm		DWG NO	36224	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					
						SHEET 1 OF 1	