




NOTES:

- 1. SUBSTRATE:  
GRADE A FINE ANNEALED
- ② COATING (APPLY ACROSS COATING APERTURE)  
NONE  
NONE
- 3. CENTERING TOLERANCE (AT 587.6nm):  
PLANO AXIS WEDGE: < 5 ARCMIN  
POWER AXIS WEDGE: < 5 ARCMIN  
AXIAL TWIST: < 3 ARCMIN
- △ 4. FINE GRIND SURFACE
- 5. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 6. FOCAL LENGHT (EFL): 50nm  
BACK FOCAL LENGTH (BFL): 47.14nm
- 7. RoHS COMPLIANT



**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2					
SHAPE	CONVEX	PLANO			TITLE	LENS PCX CYLINDER 25.40mm x 25.40mm x 50.00mm EFL	
SURFACE QUALITY	40 - 20	40 - 20					
CLEAR APERTURE	Ø22.86 x 22.86	Ø22.86 x 22.86			DWG NO	34754	SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm			