

NOTES:



1. SUBSTRATE:
N-BK7
2. COATING (APPLY ACROSS COATING APERTURE)
S1: Protected Aluminum (400-2000nm)
R(AVG) >85% @ 400 - 700nm
R(AVG) >90% @ 400 - 2000nm

DAMAGE THRESHOLD,
TYPICAL: 0.3 J/cm² @ 10ns @ 532nm & 1064nm

S2: NONE

 FINE GRIND SURFACE

4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	19.09 x 13.50	13.50 x 13.50
COATING APERTURE	19.09 x 13.50	13.50 x 13.50
SURFACE FLATNESS	λ/8	λ/8
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE 15mm, Aluminum Coated, N-BK7 High Tolerance RA Prism

DWG NO 32546 SHEET 1 OF 1