


NOTES:

1. Substrate
2. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACES
3. COATING (APPLY ACROSS COATING APERTURE)

S1: Ravg ≥ 95% @ 400 - 690nm @ 0° AOI
 Tavg ≥ 90% @ 750 - 1200nm @ 0° AOI


S2: AR Coating: Ravg <1.0% @ 700 - 1150nm @ 0° AOI

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. RoHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	Edmund Optics®			
SHAPE	PLANO	PLANO				
SURFACE FLATNESS	4 - 6λ	4 - 6λ	THIRD ANGLE PROJECTION		TITLE	Ø50mm, 0° AOI, COLD MIRROR
SURFACE QUALITY	80-50	80-50			DWG NO	64440
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm		