## NOTES:

1. SUBSTRATE MATERIAL: N-BK7

- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1: 60% R ±5% @ 550nm 40% T ±5% @ 550nm


S2: AR R(avg) ≤1%, R(abs) ≤2% @ 400 - 700nm

4.

CUT WITH 0.25mm MAXIMUM EDGE CHIP

5. ROHS COMPLIANT





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
ANGLE OF INCIDENCE	45°	45°
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm

	8	Edmund Optics®
7.11DD 4.11G15 A 1		Ø12.5mm 40.R/60.T PLATE BEAMSPLITTER

THIRD ANGLE PROJECTION	$\phi$	TITLE	Ø12.5mm, 40 R/60 T, PLATE BEAMSPLIT	TER
ALL DIMS IN	mm	DWG NO	68399	SHEET 1 OF 1