




NOTES:

- 1. SUBSTRATE: UV FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 3 arcsec
- 3. COATING SPECIFICATIONS APPLY ACROSS COATING APERTURE
 - S1: Dielectric
 - T(AVG) >90% FROM 444 - 850
 - R(AVG) >98% FROM 325 - 425
 - S2: AR
- 4. FINE GRIND SURFACE
- 5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 6. TRANSMITTED WAVEFRONT DISTORTION @ 632.8nms: $\leq \lambda/10$
- 7. ROHS COMPLIANT

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
COATING APERTURE	HARD COATED	HARD COATED
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION		TITLE	25.2 x 35.6mm, 435nm, HIGH PERFORMANCE FLUORESCENCE DICHROIC FILTER
ALL DIMS IN	mm	DWG NO	34727
			SHEET 1 OF 1