


NOTES:



1. SUBSTRATE MATERIAL: N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)
Protected Gold
S1: R(avg) >96% @ 700 - 2000
R(avg) >96% @ 2000 - 10000nm
S2: NONE
3. POWER, IRREGULARITY, SURFACE QUALITY AND COATING SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



4. FINE GRIND SURFACE

5. RoHS EXEMPT




SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	CONCAVE	CONCAVE
RADIUS	12.00	12.00
EFFECTIVE FOCAL LENGTH	6mm	N/A
FOCAL LENGTH TOLERANCE	±2%	N/A
SURFACE QUALITY	80-50	FINE GROUND
SURFACE FLATNESS	COMMERCIAL POLISH	N/A
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION



ALL DIMS IN

mm

EO® **Edmund Optics**®

TITLE

12mm Dia. x 6mm FL Protected Gold,
Concave Mirror

DWG NO

43826

SHEET
1 OF 1